



PANEL MOUNT, 3-32 VDC INPUT VOLTAGE, SPST, (1) N.O. SCR, 90A CONTACT RATING, 24-230 VAC LOAD VOLTAGE, PUSH-IN SPRING, OVERVOLTAGE PROTECTION. THERMAL MOUNTING PAD INCLUDED.

GEFRAN SOLID STATE RELAY				GQ-90-24-D-1-4			AutomationDirect.com 1-800-633-0405	
	3rd ANGLE	NOT TO SCALE	PART DIMENSIONS MAY DIFFER SLIGHTLY DUE TO MANUFACTURER'S VARIANCES	METRIC UNITS USED FOR PART DESIGN	UNLESS OTHERWISE SPECIFIED UNITS ARE:	mm [inch]	LATEST VERSION 5/28/2024	SHEET 1 OF 1