



PANEL MOUNT, 20-260 VAC INPUT VOLTAGE, SPST, (1) N.O. SCR, 90A CONTACT RATING, 48-600 VAC LOAD VOLTAGE, PUSH-IN SPRING, OVERVOLTAGE PROTECTION. THERMAL MOUNTING PAD INCLUDED.

GEFRAN SOLID STATE RELAY			GQ-90-60-A-1-4			AutomationDirect.com 1-800-633-0405	
3rd ANGLE	NOT TO SCALE	PART DIMENSIONS MAY DIFFER SLIGHTLY DUE TO MANUFACTURER'S VARIANCES	METRIC UNITS USED FOR PART DESIGN	UNLESS OTHERWISE SPECIFIED UNITS ARE:	mm [inch]	LATEST VERSION 5/28/2024	SHEET 1 OF 1