



PANEL MOUNT, 3-32 VDC INPUT VOLTAGE, SPST, (1) N.O. SCR, 90A CONTACT RATING, 48-600 VAC LOAD VOLTAGE, PUSH-IN SPRING, OVERVOLTAGE PROTECTION. THERMAL MOUNTING PAD INCLUDED.

GEFRAN SOLID STATE RELAY

GQ-90-60-D-1-4

AutomationDirect.com
1-800-633-0405



3rd
ANGLE

NOT TO
SCALE

PART DIMENSIONS MAY DIFFER SLIGHTLY
DUE TO MANUFACTURER'S VARIANCES

METRIC UNITS USED
FOR PART DESIGN

UNLESS OTHERWISE
SPECIFIED UNITS ARE:

mm
[inch]

LATEST VERSION
5/28/2024

SHEET 1 OF 1