



35mm DIN RAIL MOUNT, 20-260 VAC INPUT VOLTAGE, SPST, (1) N.O. SCR, 120A CONTACT RATING, 24-600 VAC LOAD VOLTAGE, PUSH-IN SPRING, OVERVOLTAGE AND THERMAL PROTECTION, EXTERNAL 230 VAC REQUIRED.

GEFRAN SOLID STATE RELAY WITH FAN

GRSH-120-60-A-0-60

AutomationDirect.com
1-800-633-0405



3rd
ANGLE

NOT TO
SCALE

PART DIMENSIONS MAY DIFFER SLIGHTLY
DUE TO MANUFACTURER'S VARIANCES

METRIC UNITS USED
FOR PART DESIGN

UNLESS OTHERWISE
SPECIFIED UNITS ARE:

mm
[inch]

LATEST VERSION
4/4/2024

SHEET 1 OF 1