



35mm DIN RAIL MOUNT, 20-260 VAC INPUT VOLTAGE, SPST, (1)  
N.O. SCR, 15A CONTACT RATING, 24-480 VAC LOAD VOLTAGE,  
PUSH-IN SPRING, OVERVOLTAGE PROTECTION.

## GEFRAN SOLID STATE RELAY

**GRSH-15-48-A-0-0**

AutomationDirect.com  
1-800-633-0405



3rd  
ANGLE

NOT TO  
SCALE

PART DIMENSIONS MAY DIFFER SLIGHTLY  
DUE TO MANUFACTURER'S VARIANCES

METRIC UNITS USED  
FOR PART DESIGN

UNLESS OTHERWISE  
SPECIFIED UNITS ARE:

**mm**  
[inch]

LATEST VERSION  
5/28/2024

SHEET 1 OF 1