



35mm DIN RAIL MOUNT, 20-260 VAC INPUT VOLTAGE, SPST, (1)
N.O. SCR, 15A CONTACT RATING, 24-480 VAC LOAD VOLTAGE,
PUSH-IN SPRING, OVERVOLTAGE AND THERMAL PROTECTION.
THERMAL ALARM.

GEFRAN SOLID STATE RELAY

GRSH-15-48-A-5-0

AutomationDirect.com
1-800-633-0405



3rd
ANGLE

NOT TO
SCALE

PART DIMENSIONS MAY DIFFER SLIGHTLY
DUE TO MANUFACTURER'S VARIANCES

METRIC UNITS USED
FOR PART DESIGN

UNLESS OTHERWISE
SPECIFIED UNITS ARE:

mm
[inch]

LATEST VERSION
5/28/2024

SHEET 1 OF 1