



35mm DIN RAIL MOUNT, 6-32 VDC INPUT VOLTAGE, SPST, (1) N.O.  
SCR, 15A CONTACT RATING, 24-480 VAC LOAD VOLTAGE, PUSH-IN  
SPRING, OVERVOLTAGE AND THERMAL PROTECTION.  
THERMAL/LOAD INTERRUPTION ALARM.

## GEFRAN SOLID STATE RELAY

**GRSH-15-48-D-2-0**

AutomationDirect.com  
1-800-633-0405



3rd  
ANGLE

NOT TO  
SCALE

PART DIMENSIONS MAY DIFFER SLIGHTLY  
DUE TO MANUFACTURER'S VARIANCES

METRIC UNITS USED  
FOR PART DESIGN

UNLESS OTHERWISE  
SPECIFIED UNITS ARE:

**mm**  
[inch]

LATEST VERSION  
5/28/2024

SHEET 1 OF 1