



35mm DIN RAIL MOUNT, 20-260 VAC INPUT VOLTAGE, SPST, (1) N.O.
 SCR, 50A CONTACT RATING, 24-600 VAC LOAD VOLTAGE, PUSH-IN
 SPRING, OVERVOLTAGE AND THERMAL PROTECTION. THERMAL ALARM.

GEFRAN SOLID STATE RELAY

GRSH-50-60-A-5-0

AutomationDirect.com
 1-800-633-0405



3rd
ANGLE

NOT TO
SCALE

PART DIMENSIONS MAY DIFFER SLIGHTLY
DUE TO MANUFACTURER'S VARIANCES

METRIC UNITS USED
FOR PART DESIGN

UNLESS OTHERWISE
SPECIFIED UNITS ARE:

mm
[inch]

LATEST VERSION
4/4/2024

SHEET 1 OF 1