



35mm DIN RAIL MOUNT, 20-260 VAC INPUT VOLTAGE, SPST, (1) N.O. SCR, 90A CONTACT RATING, 24-480 VAC LOAD VOLTAGE, PUSH-IN SPRING, OVERVOLTAGE AND THERMAL PROTECTION, EXTERNAL 230 VAC REQUIRED. THERMAL ALARM.

GEFRAN SOLID STATE RELAY

GRSH-90-48-A-5-60

AutomationDirect.com
1-800-633-0405

3rd ANGLE	NOT TO SCALE	PART DIMENSIONS MAY DIFFER SLIGHTLY DUE TO MANUFACTURER'S VARIANCES	METRIC UNITS USED FOR PART DESIGN	UNLESS OTHERWISE SPECIFIED UNITS ARE: mm [inch]	LATEST VERSION 4/4/2024	SHEET 1 OF 1
-----------	--------------	---------------------------------------------------------------------	-----------------------------------	--------------------------------------------------------	----------------------------	--------------