



0.16-0.25A ADJUSTABLE, BI-METALLIC, DIRECT MOUNT POWER CONNECTION(s). FOR USE WITH HMC-9 TO HMC-40 CONTACTORS.

IRONHORSE THERMAL OVERLOAD RELAY

HTOR32-0.25-S

AutomationDirect.com
1-800-633-0405



3rd
ANGLE

NOT TO
SCALE

PART DIMENSIONS MAY DIFFER SLIGHTLY
DUE TO MANUFACTURER'S VARIANCES

METRIC UNITS USED
FOR PART DESIGN

UNLESS OTHERWISE
SPECIFIED UNITS ARE:

mm
[inch]

LATEST VERSION
11/1/2022

SHEET 1 OF 1