



0.25-0.40A ADJUSTABLE, BI-METALLIC, DIRECT MOUNT POWER CONNECTION(S). FOR USE WITH HMC-9 TO HMC-40 CONTACTORS.

IRONHORSE THERMAL OVERLOAD RELAY

HTOR32-0.40-S

AutomationDirect.com
1-800-633-0405



3rd
ANGLE

NOT TO
SCALE

PART DIMENSIONS MAY DIFFER SLIGHTLY
DUE TO MANUFACTURER'S VARIANCES

METRIC UNITS USED
FOR PART DESIGN

UNLESS OTHERWISE
SPECIFIED UNITS ARE:

mm
[inch]

LATEST VERSION
11/1/2022

SHEET 1 OF 1