





WIRE RANGE: 4-18 AWG  
TORQUE: 20 IN-lbs (2.3 Nm)



AUTOMATIONDIRECT LR2 SERIES LINE REACTOR, 230 VAC, 3HP, 1-PHASE, 19A, 3% IMPEDANCE, INPUT SIDE ONLY. FOR USE WITH MULTIPLE AC DRIVES

LR2-23P0-1PH

AutomationDirect.com  
1-800-633-0405

	3rd ANGLE	NOT TO SCALE	PART DIMENSIONS MAY DIFFER SLIGHTLY DUE TO MANUFACTURER'S VARIANCES	METRIC UNITS USED FOR PART DESIGN	UNLESS OTHERWISE SPECIFIED UNITS ARE:	inch [mm]	LATEST VERSION 2/13/2024	SHEET 1 OF 1
--	-----------	--------------	---	-----------------------------------	---------------------------------------	-----------	--------------------------	--------------