




ISOMETRIC VIEW




EXTENDED VIEW



RETRACTED VIEW




M4 X 0.7 THREAD
(8-32 UNF-2A OPTIONAL)



Ø 0.50
[12.7]

JAM NUT



3.2 FT / 1 METER
CABLE LENGTH

ALLIANCE SENSORS INDUCTIVE LINEAR POSITION SENSOR, SLIDE, 50MM STROKE, 4MM SHAFT DIAMETER, 0-10 VDC OUTPUT, 12.7MM DIAMETER X 61.2MM BODY, M4 X 0.7 MOUNT, PIGTAIL, 3.2FT/1M CABLE LENGTH.

LZE13-050A-00-10S

AutomationDirect.com
1-800-633-0405



3rd
ANGLE

NOT TO
SCALE

PART DIMENSIONS MAY DIFFER SLIGHTLY
DUE TO MANUFACTURER'S VARIANCES

METRIC UNITS USED
FOR PART DESIGN

UNLESS OTHERWISE
SPECIFIED UNITS ARE:

inch
[mm]

LATEST VERSION
3/18/2022

SHEET 1 OF 1