



ISOMETRIC VIEW



PROSENSE MAGNETIC PROXIMITY SENSOR, TUBULAR, 18MM DIAMETER X 60MM BODY, STAINLESS STEEL HOUSING, PNP, N.O. OUTPUT, 70MM SENSING DISTANCE, FLUSH, 5 KHZ SWITCHING FREQUENCY, IP65 IP68 IP69K, 4-PIN M12 QUICK-DISCONNECT.

**MAFK1-AP-1H**

AutomationDirect.com  
1-800-633-0405



3rd  
ANGLE

NOT TO  
SCALE

PART DIMENSIONS MAY DIFFER SLIGHTLY  
DUE TO MANUFACTURER'S VARIANCES

METRIC UNITS USED  
FOR PART DESIGN

UNLESS OTHERWISE  
SPECIFIED UNITS ARE:

**mm**  
[inch]

LATEST VERSION  
2/28/2023

SHEET 1 OF 1