



ISOMETRIC VIEW



PROSENSE MAGNETIC PROXIMITY SENSOR, TUBULAR, 12MM DIAMETER X 60MM BODY, STAINLESS STEEL HOUSING, PNP, N.O. OUTPUT, 60MM SENSING DISTANCE, FLUSH, 5 KHZ SWITCHING FREQUENCY, IP65 IP68 IP69K, 4-PIN M12 QUICK-DISCONNECT.

MAFM1-AP-1H

AutomationDirect.com
1-800-633-0405



3rd
ANGLE

NOT TO
SCALE

PART DIMENSIONS MAY DIFFER SLIGHTLY
DUE TO MANUFACTURER'S VARIANCES

METRIC UNITS USED
FOR PART DESIGN

UNLESS OTHERWISE
SPECIFIED UNITS ARE:

mm
[inch]

LATEST VERSION
2/28/2023

SHEET 1 OF 1