



IronHorse MTS SERIES PREMIUM EFFICIENCY AC INDUCTION MOTOR, WASHDOWN, INVERTER RATED & HAZARDOUS LOCATION, 1HP, 3-PH, 208-230/460 VAC, 3600RPM, TENV, 56C FRAME, 304 SS, RIGID BASE/C-FACE MOUNT

MTSN-001-3BD36

AutomationDirect.com
1-800-633-0405

	3rd ANGLE	NOT TO SCALE	PART DIMENSIONS MAY DIFFER SLIGHTLY DUE TO MANUFACTURER'S VARIANCES	INCH UNITS USED FOR PART DESIGN	UNLESS OTHERWISE SPECIFIED UNITS ARE:	inch [mm]	LATEST VERSION 4/18/2022	SHEET 1 OF 1
--	-----------	--------------	---	---------------------------------	---------------------------------------	-----------	--------------------------	--------------