



IronHorse MTS SERIES PREMIUM EFFICIENCY AC INDUCTION MOTOR, WASHDOWN, INVERTER RATED & HAZARDOUS LOCATION, 2HP, 3-PH, 208-230/460 VAC, 1800RPM, TENV, 56C FRAME, 304 SS, RIGID BASE/C-FACE MOUNT

MTSN-002-3BD18

AutomationDirect.com  
1-800-633-0405



3rd  
ANGLE

NOT TO  
SCALE

PART DIMENSIONS MAY DIFFER SLIGHTLY  
DUE TO MANUFACTURER'S VARIANCES

INCH UNITS USED FOR  
PART DESIGN

UNLESS OTHERWISE  
SPECIFIED UNITS ARE:

inch  
[mm]

LATEST VERSION  
4/19/2022

SHEET 1 OF 1