



IronHorse MTS SERIES PREMIUM EFFICIENCY AC INDUCTION MOTOR, WASHDOWN, INVERTER RATED & HAZARDOUS LOCATION, 1-1/2HP, 3-PH, 208-230/460 VAC, 1800RPM, TENV, 56C FRAME, 304 SS, RIGID BASE/C-FACE MOUNT

MTSN-1P5-3BD18

AutomationDirect.com
1-800-633-0405



3rd
ANGLE

NOT TO
SCALE

PART DIMENSIONS MAY DIFFER SLIGHTLY
DUE TO MANUFACTURER'S VARIANCES

INCH UNITS USED FOR
PART DESIGN

UNLESS OTHERWISE
SPECIFIED UNITS ARE:

inch
[mm]

LATEST VERSION
4/18/2022

SHEET 1 OF 1