



IronHorse MTS SERIES PREMIUM EFFICIENCY AC INDUCTION MOTOR, WASHDOWN, INVERTER RATED & HAZARDOUS LOCATION, 2HP, 3-PH, 208-230/460 VAC, 1200RPM, TEFC, 184TC FRAME, 304 SS, RIGID BASE/C-FACE MOUNT

3rd ANGLE