



0.19 X 0.19
X 1.41 KEY



DETAIL A
SCALE 2:1



IronHorse MTS SERIES PREMIUM EFFICIENCY AC INDUCTION MOTOR, WASHDOWN, INVERTER RATED & HAZARDOUS LOCATION, 2HP, 3-PH, 208-230/460 VAC, 1800RPM, TEFC, 145TC FRAME, 304 SS, RIGID BASE/C-FACE MOUNT

MTSP-002-3BD18-14

AutomationDirect.com
1-800-633-0405



3rd
ANGLE

NOT TO
SCALE

PART DIMENSIONS MAY DIFFER SLIGHTLY
DUE TO MANUFACTURER'S VARIANCES

INCH UNITS USED FOR
PART DESIGN

UNLESS OTHERWISE
SPECIFIED UNITS ARE:

inch
[mm]

LATEST VERSION
3/30/2022

SHEET 1 OF 1