



IronHorse MTS SERIES PREMIUM EFFICIENCY AC INDUCTION MOTOR, WASHDOWN, INVERTER RATED & HAZARDOUS LOCATION, 3HP, 3-PH, 208-230/460 VAC, 1800RPM, TEFC, 182TC FRAME, 304 SS, RIGID BASE/C-FACE MOUNT