



IronHorse MTS SERIES PREMIUM EFFICIENCY AC INDUCTION MOTOR, WASHDOWN, INVERTER RATED & HAZARDOUS LOCATION, 1-1/2HP, 3-PH, 208-230/460 VAC, 1800RPM, TEFC, 56C FRAME, 304 SS, RIGID BASE/C-FACE MOUNT

**MTSP-1P5-3BD18**

AutomationDirect.com  
1-800-633-0405

	3rd ANGLE	NOT TO SCALE	PART DIMENSIONS MAY DIFFER SLIGHTLY DUE TO MANUFACTURER'S VARIANCES	INCH UNITS USED FOR PART DESIGN	UNLESS OTHERWISE SPECIFIED UNITS ARE:	inch [mm]	LATEST VERSION 6/2/2022	SHEET 1 OF 1
--	-----------	--------------	---	---------------------------------	---------------------------------------	-----------	-------------------------	--------------