




SUB PANEL (ORDER SEPARATELY)
SECTION B-B



SPECIAL REQUIREMENTS

- BONDED WINDOWS**
1. ROUTE COVER FACE DOWN AND REMOVE THE TWO MOUNTING BOSS WHEN REQUIRED.
 2. ROUGH BOTH SURFACES BEFORE BONDING. MINIMUM OVERLAP BETWEEN THE WINDOW OPENING SIZES UP TO 1/4" (6.35) AND A MINIMUM 0.375" THICKNESS FOR OPENINGS OVER 1/4" (6.35). THE BONDING SURFACES MUST BE FLAT AND FREE OF OIL, DIRT, AND OTHER CONTAMINANTS. THE BONDING SURFACES MUST BE FLAT AND FREE OF OIL, DIRT, AND OTHER CONTAMINANTS. THE BONDING SURFACES MUST BE FLAT AND FREE OF OIL, DIRT, AND OTHER CONTAMINANTS.
- SPECIFICATIONS: 1) 125°-200° & 200°-275°-300° & -060°
ACRYLIC #2: NOMINAL SIZE 0.375" (9.5)
UL FILE #E84598 VOL. 1: SECOGEN TYPE RATINGS 1.3R-4X-12