



WENGLOR ULTRASONIC PROXIMITY SENSOR, TUBULAR, 18MM DIAMETER X 86MM BODY, STAINLESS STEEL HOUSING, 0-10 VDC
ANALOG OUTPUT, N.O., 50-400MM SENSING DISTANCE, 20 HZ SWITCHING FREQUENCY, IP67, 4-PIN M12 QUICK-DISCONNECT

OPT2210

AutomationDirect.com
1-800-633-0405



3rd
ANGLE

NOT TO
SCALE

PART DIMENSIONS MAY DIFFER SLIGHTLY
DUE TO MANUFACTURER'S VARIANCES

METRIC UNITS USED
FOR PART DESIGN

UNLESS OTHERWISE
SPECIFIED UNITS ARE:

mm
[inch]

LATEST VERSION
3/21/2023

SHEET 1 OF 1