



OPTRIS CS LT IR PYROMETER, -50 to 1030 °C, 8-14 µm SPECTRAL RANGE, 0-5 VDC, 0-10 VDC, TYPE K THERMOCOUPLE OR ALARM OUTPUT, 5-30 VDC OPERATING, M12x1 THREADED END MOUNT, 1m INTEGRAL 7-CONDUCTOR SHIELDED CABLE

OPTCSLT15SFCB1

AutomationDirect.com
1-800-633-0405



3rd
ANGLE

NOT TO
SCALE

PART DIMENSIONS MAY DIFFER SLIGHTLY
DUE TO MANUFACTURER'S VARIANCES

METRIC UNITS USED
FOR PART DESIGN

UNLESS OTHERWISE
SPECIFIED UNITS ARE:

mm
[inch]

LATEST VERSION
5/2/2022

SHEET 1 OF 1