


ISOMETRIC VIEW



ACHIEVE INDUCTIVE PROXIMITY SENSOR, TUBULAR, 18MM DIAMETER X 63.5MM BODY, NICKEL-PLATED BRASS HOUSING, NPN, N.O. OUTPUT, 8MM SENSING DISTANCE, NON-FLUSH, 2 KHZ SWITCHING FREQUENCY, IP67, 4-PIN M12 QUICK-DISCONNECT.

**PAK-AN-2H**

AutomationDirect.com  
1-800-633-0405



3rd  
ANGLE

NOT TO  
SCALE

PART DIMENSIONS MAY DIFFER SLIGHTLY  
DUE TO MANUFACTURER'S VARIANCES

METRIC UNITS USED  
FOR PART DESIGN

UNLESS OTHERWISE  
SPECIFIED UNITS ARE:

**mm**  
[inch]

LATEST VERSION  
10/11/2023

SHEET 1 OF 1