


ISOMETRIC VIEW



ACHIEVE INDUCTIVE PROXIMITY SENSOR, TUBULAR, 18MM DIAMETER X 63.5MM BODY, NICKEL-PLATED BRASS HOUSING, PNP, N.O. OUTPUT, 5MM SENSING DISTANCE, FLUSH, 2 KHZ SWITCHING FREQUENCY, IP67, 4-PIN M12 QUICK-DISCONNECT.

PAK-AP-1H

AutomationDirect.com
1-800-633-0405



3rd
ANGLE

NOT TO
SCALE

PART DIMENSIONS MAY DIFFER SLIGHTLY
DUE TO MANUFACTURER'S VARIANCES

METRIC UNITS USED
FOR PART DESIGN

UNLESS OTHERWISE
SPECIFIED UNITS ARE:

mm
[inch]

LATEST VERSION
10/11/2023

SHEET 1 OF 1