


ISOMETRIC VIEW



ACHIEVE INDUCTIVE PROXIMITY SENSOR, TUBULAR, 12MM DIAMETER X 60MM BODY, NICKEL-PLATED BRASS HOUSING, NPN, N.O. OUTPUT, 4MM SENSING DISTANCE, NON-FLUSH, 2 KHZ SWITCHING FREQUENCY, IP67, 4-PIN M12 QUICK-DISCONNECT.

PAM-AN-2H

AutomationDirect.com
1-800-633-0405



3rd
ANGLE

NOT TO
SCALE

PART DIMENSIONS MAY DIFFER SLIGHTLY
DUE TO MANUFACTURER'S VARIANCES

METRIC UNITS USED
FOR PART DESIGN

UNLESS OTHERWISE
SPECIFIED UNITS ARE:

mm
[inch]

LATEST VERSION
10/12/2023

SHEET 1 OF 1