


ISOMETRIC VIEW



ACHIEVE INDUCTIVE PROXIMITY SENSOR, TUBULAR, 12MM DIAMETER X 35MM BODY, NICKEL-PLATED BRASS HOUSING, PNP, N.O. OUTPUT, 2MM SENSING DISTANCE, FLUSH, 3 KHZ SWITCHING FREQUENCY, IP67, PIGTAIL.

**PAM-AP-1A**

AutomationDirect.com  
1-800-633-0405



3rd  
ANGLE

NOT TO  
SCALE

PART DIMENSIONS MAY DIFFER SLIGHTLY  
DUE TO MANUFACTURER'S VARIANCES

METRIC UNITS USED  
FOR PART DESIGN

UNLESS OTHERWISE  
SPECIFIED UNITS ARE:

**mm**  
[inch]

LATEST VERSION  
10/12/2023

SHEET 1 OF 1