



THREAD ASME MNPT 1/2,  
 FNPT 1/4, 316L

ENDRESS+HAUSER PRESSURE TRANSMITTER, 0-6 psig RANGE,  $\pm 0.5\%$  OF FULL RANGE ACCURACY, CERAMIC SENSING ELEMENT, FKM SEAL(S), 4-20mA ANALOG OUTPUT, 1/2in MALE NPT OR 1/4in FEMALE NPT PROCESS CONNECTION, 10-30 VDC OPERATING VOLTAGE, 4-PIN M12 QUICK-DISCONNECT

**PMC11-CA1L1FFVXJA**

AutomationDirect.com  
 1-800-633-0405



3rd  
 ANGLE

NOT TO  
 SCALE

PART DIMENSIONS MAY DIFFER SLIGHTLY  
 DUE TO MANUFACTURER'S VARIANCES

METRIC UNITS USED  
 FOR PART DESIGN

UNLESS OTHERWISE  
 SPECIFIED UNITS ARE:

**mm**  
**[inch]**

LATEST VERSION  
 9/25/2023

SHEET 1 OF 1