



ISOMETRIC VIEW

SCHMERSAL COMPACT LIMIT SWITCH, PLUNGER WITH PLASTIC ROLLER, 45-DEGREE ADJUSTABLE HEAD, (1) N.O./ (1) N.C. CONTACT(S), SLOW ACTION BREAK BEFORE MAKE, 31MM WIDE BODY, 20-22MM HOLE SPACING, DIE-CAST ZINC WITH PLASTIC BASE, PIGTAIL, 6.5FT/2M CABLE LENGTH, BOTTOM EXIT, GROSS WEIGHT = 0.38 LBS.

PS116T11-L200R200

AutomationDirect.com
1-800-633-0405



3rd
ANGLE

NOT TO
SCALE

PART DIMENSIONS MAY DIFFER SLIGHTLY
DUE TO MANUFACTURER'S VARIANCES

METRIC UNITS USED
FOR PART DESIGN

UNLESS OTHERWISE
SPECIFIED UNITS ARE:

mm
[inch]

LATEST VERSION
10/27/2022

SHEET 1 OF 1