



SCHMERSAL COMPACT LIMIT SWITCH, SIDE ROTARY LEVER WITH PLASTIC ROLLER, 45-DEGREE ADJUSTABLE HEAD, (1) N.O./ (1) N.C. CONTACT(S), SLOW ACTION
 BREAK BEFORE MAKE, 31MM WIDE BODY, 20-22MM HOLE SPACING, DIE-CAST ZINC WITH PLASTIC BASE, 4-PIN M12 QUICK-DISCONNECT, GROSS WEIGHT =
 0.24LBS.

PS116T11-STRH200

AutomationDirect.com
 1-800-633-0405



3rd
 ANGLE

NOT TO
 SCALE

PART DIMENSIONS MAY DIFFER SLIGHTLY
 DUE TO MANUFACTURER'S VARIANCES

METRIC UNITS USED
 FOR PART DESIGN

UNLESS OTHERWISE
 SPECIFIED UNITS ARE:

mm
[inch]

LATEST VERSION
 10/27/2022

SHEET 1 OF 1