



SCHMERSAL COMPACT LIMIT SWITCH, PLUNGER WITH PLASTIC ROLLER, 45-DEGREE ADJUSTABLE HEAD, (1) N.O./ (1) N.C. CONTACT(S), SNAP ACTION, 31MM WIDE BODY, 20-22MM HOLE SPACING, DIE-CAST ZINC WITH PLASTIC BASE, PIGTAIL, 6.5FT/2M CABLE LENGTH, BOTTOM EXIT, GROSS WEIGHT = 0.41LBS.

PS116Z11-L200R200

AutomationDirect.com
1-800-633-0405

	3rd ANGLE	NOT TO SCALE	PART DIMENSIONS MAY DIFFER SLIGHTLY DUE TO MANUFACTURER'S VARIANCES	METRIC UNITS USED FOR PART DESIGN	UNLESS OTHERWISE SPECIFIED UNITS ARE:	mm [inch]	LATEST VERSION 10/27/2022	SHEET 1 OF 1
--	-----------	--------------	---	-----------------------------------	---------------------------------------	-----------	---------------------------	--------------