




ITEM	DEVICE DESCRIPTION
1	INPUT TERMINAL BLOCK CONNECTOR
	PIN 1: PE
	PIN 2: L1
	PIN 3: L2
	PIN 4: L3
2	OUTPUT TERMINAL BLOCK CONNECTOR
	PIN 1 TO 2: V(+)
	PIN 3 TO 4: V(-)
3	DC OK RELAY CONTACT



ISOMETRIC VIEW



RHINO PSR SERIES SWITCHING POWER SUPPLY, 24-28 VDC OUTPUT, 40A, 960W, 480 VAC NOMINAL INPUT, 3-PHASE, ENCLOSED, ALUMINUM HOUSING, 35MM DIN RAIL MOUNT, SCREW TERMINALS.

PSR-24-960-3

AutomationDirect.com
1-800-633-0405



3rd
ANGLE

NOT TO
SCALE

PART DIMENSIONS MAY DIFFER SLIGHTLY
DUE TO MANUFACTURER'S VARIANCES

METRIC UNITS USED
FOR PART DESIGN

UNLESS OTHERWISE
SPECIFIED UNITS ARE:

mm
[inch]

LATEST VERSION
2/10/2023

SHEET 1 OF 1