


ISOMETRIC VIEW



PINOUT		
PIN	FUNCTION	RECOMMENDED WIRE
1	+Vin	14-16 AWG
2	+Vin	14-16 AWG
3	-Vin	14-16 AWG
4	-Vin	14-16 AWG
5	Remote	14-24 AWG
6	+Vout	14-16 AWG
7	-Vout	14-16 AWG
8	Trim	14-24 AWG
9	Trim	14-24 AWG

RHINO PRO DC TO DC CONVERTER, 18-75 VDC INPUT, 24 VDC OUTPUT, 6.3A, 150W, ALUMINUM HOUSING, ENCAPSULATED, CHASSIS MOUNT, SCREW TERMINAL.

**PSRP-24-DC48-150**

AutomationDirect.com  
1-800-633-0405



3rd  
ANGLE

NOT TO  
SCALE

PART DIMENSIONS MAY DIFFER SLIGHTLY  
DUE TO MANUFACTURER'S VARIANCES

METRIC UNITS USED  
FOR PART DESIGN

UNLESS OTHERWISE  
SPECIFIED UNITS ARE:

**mm**  
[inch]

LATEST VERSION  
10/18/2022

SHEET 1 OF 1