



2-PORT (2-WAY), 2-POSITION, N.C., NYLON BODY, VITON SEAL(S), 1/4IN FEMALE NPT INLET(S), 1/4IN FEMALE NPT OUTLET(S), CV=0.28, 0 PSI MINIMUM OPERATING PRESSURE, 24 VDC OPERATING VOLTAGE, 11mm DIN STYLE WIRING PLUG.

CFA SOLENOID VALVE

SC311YN16VIBA5

AutomationDirect.com
1-800-633-0405

3rd ANGLE	NOT TO SCALE	PART DIMENSIONS MAY DIFFER SLIGHTLY DUE TO MANUFACTURER'S VARIANCES	INCH UNITS USED FOR PART DESIGN	UNLESS OTHERWISE SPECIFIED UNITS ARE:	inch [mm]	LATEST VERSION 12/20/2023	SHEET 1 OF 1
-----------	--------------	---	---------------------------------	---------------------------------------	---------------------	------------------------------	--------------