



2-PORT (2-WAY), 2-POSITION, N.C., STAINLESS STEEL BODY, VITON SEAL(s), 1/8IN FEMALE NPT INLET(s), 1/8IN FEMALE NPT OUTLET(s), CV=0.14, 0 PSI MINIMUM OPERATING PRESSURE, 24 VAC OPERATING VOLTAGE, 11mm DIN STYLE WIRING PLUG.

CFA SOLENOID VALVE

SC911YN24VFAA5

AutomationDirect.com
1-800-633-0405

| | | | | | | | |
|-----------|--------------|---|---------------------------------|---------------------------------------|---------------------|------------------------------|--------------|
| 3rd ANGLE | NOT TO SCALE | PART DIMENSIONS MAY DIFFER SLIGHTLY DUE TO MANUFACTURER'S VARIANCES | INCH UNITS USED FOR PART DESIGN | UNLESS OTHERWISE SPECIFIED UNITS ARE: | inch [mm] | LATEST VERSION 12/20/2023 | SHEET 1 OF 1 |
|-----------|--------------|---|---------------------------------|---------------------------------------|---------------------|------------------------------|--------------|