



STRIDE INDUSTRIAL UNMANAGED ETHERNET SWITCH, 5 PORTS, (4) ETHERNET 10/100Base-T (RJ45) PORTS(S) and (1) MULTI-MODE SC 100FX FIBER PORT(S), -40 to +75 DEG C, METAL HOUSING, IP30, NEMA TS2, 35mm DIN RAIL OR PANEL MOUNT

SE3-SW5U-1C1-T

AutomationDirect.com
1-800-633-0405



3rd
ANGLE

NOT TO
SCALE

PART DIMENSIONS MAY DIFFER SLIGHTLY
DUE TO MANUFACTURER'S VARIANCES

INCH UNITS USED FOR
PART DESIGN

UNLESS OTHERWISE
SPECIFIED UNITS ARE:

mm
[inch]

LATEST VERSION
8/9/2023

SHEET 1 OF 1