



STRIDE INDUSTRIAL UNMANAGED ETHERNET SWITCH, 6 PORTS, (4) ETHERNET 10/100Base-T (RJ45) PORTS(S) and (2) MULTI-MODE ST 100FX FIBER PORT(S), -40 to +75 DEG C, METAL HOUSING, IP30, 35mm DIN RAIL OR PANEL MOUNT

SE3-SW6U-2T1-T

AutomationDirect.com
1-800-633-0405



3rd
ANGLE

NOT TO
SCALE

PART DIMENSIONS MAY DIFFER SLIGHTLY
DUE TO MANUFACTURER'S VARIANCES

INCH UNITS USED FOR
PART DESIGN

UNLESS OTHERWISE
SPECIFIED UNITS ARE:

mm
[inch]

LATEST VERSION
8/14/2023

SHEET 1 OF 1