



STRIDE INDUSTRIAL UNMANAGED PoE+ SWITCH, 120W, 5 PORTS, (4) PoE+ Gigabit (RJ45), AND (1) ETHERNET 10/100Base-T (RJ45) PORTS(S), 12-36 VDC NOMINAL INPUT, -40 to +75 DEG C, METAL HOUSING, IP30, NEMA TS2, 35mm DIN RAIL OR PANEL MOUNT, HAZARDOUS LOCATION RATED

SE3-SWP2A5UG-T

AutomationDirect.com
1-800-633-0405



3rd
ANGLE

NOT TO
SCALE

PART DIMENSIONS MAY DIFFER SLIGHTLY
DUE TO MANUFACTURER'S VARIANCES

INCH UNITS USED FOR
PART DESIGN

UNLESS OTHERWISE
SPECIFIED UNITS ARE:

mm
[inch]

LATEST VERSION
9/26/2023

SHEET 1 OF 1