



STRIDE INDUSTRIAL UNMANAGED PoE+ SWITCH, 60W @ 12-36 VDC, 120W @ 37-55 VDC, 7 PORTS, (4) PoE+ 10/100Base-T (RJ45), (1) ETHERNET 10/100Base-T (RJ45) AND (2) SFP Gigabit PORTS(S), 12-55 VDC NOMINAL INPUT, -40 to +75 DEG C, METAL HOUSING, IP30

SE3-SWP2A7U-2P-T

AutomationDirect.com
1-800-633-0405



3rd
ANGLE

NOT TO
SCALE

PART DIMENSIONS MAY DIFFER SLIGHTLY
DUE TO MANUFACTURER'S VARIANCES

INCH UNITS USED FOR
PART DESIGN

UNLESS OTHERWISE
SPECIFIED UNITS ARE:

mm
[inch]

LATEST VERSION
8/14/2023

SHEET 1 OF 1