



Some versions of SV2C-PC12-xxxx are manufactured with fork terminals. If used with a SV2A-2150 drive, remove the U,V,W forks and strip the insulation back far enough to insert into the drive's spring cage terminals. Tinning the leads is recommended.

| CABLES | | |
|----------------|---------------|---------------|
| CABLE PART # | LENGTH L (IN) | LENGTH L (mm) |
| SV2C-PC12-03FN | 118 | 3000 |
| SV2C-PC12-05FN | 197 | 5000 |
| SV2C-PC12-10FN | 394 | 10000 |
| SV2C-PC12-20FN | 787 | 20000 |

NOTES:

1. DIMENSIONS CAN BE CHANGED BY MANUFACTURER WITHOUT NOTICE.
2. DIMENSIONS DO NOT IMPLY TOLERANCE.

SV2C-PC12-20FN

Units: mm [inch]
Full Scale

SureServo2 POWER FLEX CABLE, MATING CONNECTIONS, 65.6FT/20m CABLE LENGTH, FOR USE WITH 1 kW MEDIUM INERTIA AND 1.5 kW SureServo2 MOTORS WITHOUT BRAKE

AUTOMATIONDIRECT.com