



ONBOARD  
ADJUSTABLE  
ONLY



1 TO 100 SECONDS TIMING RANGE, 120 VAC/VDC OPERATING VOLTAGE,  
30A CONTACT RATING, (1) SPDT TIMED RELAY OUTPUT(s), SURFACE  
MOUNT, 1/4IN MALE QUICK-CONNECT TERMINAL.

## PROSENSE CYCLIC RELAY TIMER

**T30R-RC-31-120A**

AutomationDirect.com  
1-800-633-0405



3rd  
ANGLE

NOT TO  
SCALE

PART DIMENSIONS MAY DIFFER SLIGHTLY  
DUE TO MANUFACTURER'S VARIANCES

INCH UNITS USED FOR  
PART DESIGN

UNLESS OTHERWISE  
SPECIFIED UNITS ARE:

**inch**  
[mm]

LATEST VERSION  
8/9/2023

SHEET 1 OF 1