



ONBOARD
ADJUSTABLE
ONLY



1 TO 100 MINUTES TIMING RANGE, 120 VAC/VDC OPERATING VOLTAGE,
30A CONTACT RATING, (1) SPDT TIMED RELAY OUTPUT(s), SURFACE
MOUNT, 1/4IN MALE QUICK-CONNECT TERMINAL.

PROSENSE CYCLIC RELAY TIMER

T30R-RC-33-120A

AutomationDirect.com
1-800-633-0405



3rd
ANGLE

NOT TO
SCALE

PART DIMENSIONS MAY DIFFER SLIGHTLY
DUE TO MANUFACTURER'S VARIANCES

INCH UNITS USED FOR
PART DESIGN

UNLESS OTHERWISE
SPECIFIED UNITS ARE:

inch
[mm]

LATEST VERSION
8/9/2023

SHEET 1 OF 1