



ONBOARD  
ADJUSTABLE  
ONLY



0.1 TO 10 MINUTES TIMING RANGE, 24 VAC/VDC OPERATING VOLTAGE, 30A CONTACT RATING, (1) SPDT TIMED RELAY OUTPUT(S), SURFACE MOUNT, 1/4IN MALE QUICK-CONNECT TERMINAL.

## PROSENSE FLEETING RELAY TIMER

T30R-SST-32-24AD

AutomationDirect.com  
1-800-633-0405



3rd  
ANGLE

NOT TO  
SCALE

PART DIMENSIONS MAY DIFFER SLIGHTLY  
DUE TO MANUFACTURER'S VARIANCES

INCH UNITS USED FOR  
PART DESIGN

UNLESS OTHERWISE  
SPECIFIED UNITS ARE:

inch  
[mm]

LATEST VERSION  
8/9/2023

SHEET 1 OF 1