



FANDIS VIRDIS SERIES EXHAUST FAN, TOP MOUNT, 288 CFM, 115 VAC OPERATING VOLTAGE, G2 (COARSE) FILTER MAT, NEMA 12, INDOOR USE ONLY, 6.89 X 6.89IN ENCLOSURE CUTOUT, RAL 7035 LIGHT GRAY.

**TP19U115B541**

AutomationDirect.com  
1-800-633-0405



3rd  
ANGLE

NOT TO  
SCALE

PART DIMENSIONS MAY DIFFER SLIGHTLY  
DUE TO MANUFACTURER'S VARIANCES

METRIC UNITS USED  
FOR PART DESIGN

UNLESS OTHERWISE  
SPECIFIED UNITS ARE:

**mm**  
**[inch]**

LATEST VERSION  
3/23/2022

SHEET 1 OF 1