



ProSense VIBRATION SWITCH/TRANSMITTER, 0-25mm/s RMS, 10-1000Hz, SWITCH OR CURRENT OUTPUT, M8 X 1.25
MALE THREADS PROCESS CONNECTION, 4-PIN M12 QUICK-DISCONNECT, 18-32 VDC OPERATING VOLTAGE, IP67

VCST-25-1000

AutomationDirect.com
1-800-633-0405



3rd
ANGLE

NOT TO
SCALE

PART DIMENSIONS MAY DIFFER SLIGHTLY
DUE TO MANUFACTURER'S VARIANCES

METRIC UNITS USED
FOR PART DESIGN

UNLESS OTHERWISE
SPECIFIED UNITS ARE:

mm
[inch]

LATEST VERSION
4/18/2022

SHEET 1 OF 1