



ProSense VIBRATION TRANSMITTER, 0-50 mm/s RMS, 10-1000Hz, 4-20 mA OUTPUT, 1/4-28 UNF FEMALE
PROCESS CONNECTION, 4-PIN M12 QUICK-DISCONNECT, 9.6-32 VDC OPERATING VOLTAGE, IP67 IP68 IP69K

VCT-50-1000

AutomationDirect.com
1-800-633-0405



3rd
ANGLE

NOT TO
SCALE

PART DIMENSIONS MAY DIFFER SLIGHTLY
DUE TO MANUFACTURER'S VARIANCES

METRIC UNITS USED
FOR PART DESIGN

UNLESS OTHERWISE
SPECIFIED UNITS ARE:

mm
[inch]

LATEST VERSION
11/15/2022

SHEET 1 OF 1