



WEIGHT DISTRIBUTION SHELF DIMENSION TABLE							
-	WD105	WD106	WD12	WD14	WD168	WD1610	WD24
A	3.50	4.40	4.40	6.40	6.50	8.40	8.40
B	10.50	10.50	12.50	14.50	16.45	16.45	24.50
C	.19	.19	.19	.19	.25	.25	.25



- NOTES:**
1. PANEL SHALL BE FREE FROM BURRS & SHARP EDGES
 2. PANEL SHALL BE FLAT
 3. MISALIGNED EDGES EXCEEDING 0.005" (STEPS) SHALL NOT BE PERMITTED
 4. ALL EDGES SHALL BE SQUARE AND PARALLEL
 5. PANEL SHALL HAVE CLEAR PVC FILM ON ONE SIDE
 6. ALL "16" SIZE PANELS AND BELOW SHALL BE PACKAGED IN AN ENVELOPE WITH NO METAL (CLASP)
 7. "24" SIZE PANEL SHALL BE PACKAGED IN CARDBOARD WITH NO METAL (STAPLES)


THIS DRAWING IS THE SOLE AND EXCLUSIVE
PROPERTY OF ROBROY ENCLOSURES.
NO PART OF THIS DRAWING MAY BE
REPRODUCED, DISTRIBUTED, OR PUBLICALLY
DISPLAYED IN ANY FORM OR BY ANY MEANS
WITHOUT THE EXPRESS WRITTEN
PERMISSION OF ROBROY ENCLOSURES.
ALL RIGHTS RESERVED
UNDER THE COPYRIGHT LAWS.
COPYRIGHT © 2022 ROBROY ENCLOSURES

SPECIAL REQUIREMENTS

ASSEMBLY:
1. (1) SLOT NUT KIT (PCSNK) INCLUDED
2. PACK IN POLY MAILER
-FOLD EXCESS MATERIAL AROUND PANEL AND TAPE TIGHT
-PLACE 4X3 LABEL ON OUTSIDE OF TAPED MAILER

END USER NOTES

1. SLOT-NUT KIT INSTALLATION
- TORQUE SCREWS TO 16 IN.-LBS
2. 150 lb. RECOMMENDED SHELF LOAD LIMIT

NEMA 250: TYPE N/A IEC 60529: N/A		STANDARD PIN: N/A		ALL DIMENSIONS ARE IN INCHES UNLESS OTHERWISE SPECIFIED		TOLERANCES UNLESS SPECIFIED		.XX ± 0.03 .XXX ± 0.010	
COLOR: N/A COLOR STANDARD: N/A		CUSTOMER DWG: N/A							
MATERIAL: ALUMINUM									
REVISION HISTORY				 AttaBox A ROBROY ENCLOSURES™ BRAND		Robroy Enclosures 500 Maple Street Belding, Michigan 48809 Phone: 616-794-0700 Fax: 616-749-3378			
REV	DESCRIPTION	DATE	ENG						
-	-	-	-						
-	-	-	-						
-	-	-	-						
-	-	-	-						
-	-	-	-						
DRAWN BY BH		DATE 12/30/22		CUSTOMER ROBROY ENCLOSURES				DWG WD12	
SCALE DO NOT SCALE		DESCRIPTION WEIGHT DISTRIBUTION SHELF		PART NUMBER WD12					



Robroy Enclosures
500 Maple Street
Belding, Michigan 48809
Phone: 616-794-0700
Fax: 616-749-3378