



ProSense TEMPERATURE TRANSMITTER, NON-ISOLATED, Pt100 RTD INPUT, 0-100 DEG F FIXED, 4-20 mA OUTPUT, 10-36 VDC OPERATING VOLTAGE, DIN FORM B CONNECTION HEAD MOUNT, SCREW TERMINALS

**XTH2-0100F-PT1**

AutomationDirect.com  
1-800-633-0405



3rd  
ANGLE

NOT TO  
SCALE

PART DIMENSIONS MAY DIFFER SLIGHTLY  
DUE TO MANUFACTURER'S VARIANCES

INCH UNITS USED FOR  
PART DESIGN

UNLESS OTHERWISE  
SPECIFIED UNITS ARE:

**mm**  
[inch]

LATEST VERSION  
5/23/2023

SHEET 1 OF 1